

ERGO 100 incl. Safety break resistance

PCSCHEMATIC Automation

A/S WODSCHOW & Co.
Kirkebjerg Søpark 6
DK-2605 Brøndby, Denmark
www.bearvarimixer.dk



Project title: ERGO 100	Case no.:	Project rev.:	Page 1
Customer:			Scale: 1:1
Page title: front page	Dwg. no.:	Page rev.:	Previous page:
File name: 34.100-10.03.04_external_use	Eng. (proj/page): CE / CE	Last print: 15-10-2018	Next page: 2
Page ref.:	Appr. (date/init):	Last edit: 28-12-2016	Total no. of pages: 25

Documentation Info

This electrical documentation fits ERGO 100

- Includes brake resistance
- ENG. version
- CE approval
- Safety relay delayed stop function

Notes

There will be several variants of charts like this:

- 1: With and without brakes
- 2: With and without transformer
- 3: UL or CE approvals

Further, it should be noted that there will be some old versions which will be phase objections along the way, this problem will this be rectified.


Revision descriptions

- Rev. 01 Drawing. no. 01, page 5 & 7: Brake Resistance + Safety relay incl. delay stop function added




Project title: ERGO 100	Case no.:	Project rev.:	Page 4
Customer:			Scale: 1:1
Page title: Diagram	Dwg. no.:	Page rev.:	Previous page: 3
File name: 34.100-10.03.04_external_use	Eng. (proj/page): CE	Last print: 15-10-2018	Next page: 5
Page ref.:	Appr. (date/init):	Last edit: 15-10-2018	Total no. of pages: 25

Diagram




Project title: ERGO 100	Case no.:	Project rev.:	Page 5
Customer:			Scale: 1:1
Page title: Diagram	Dwg. no.: 01	Page rev.: 01	Previous page: 4
File name: 34.100-10.03.04_external_use	Eng. (proj/page): CE / CE	Last print: 15-10-2018	Next page: 6
Page ref.:	Appr. (date/init):	Last edit: 15-10-2018	Total no. of pages: 25

Front panel print VL-4




Project title: ERGO 100	Case no.:	Project rev.:	Page 6
Customer:			Scale: 1:1
Page title: Diagram	Dwg. no.: 01	Page rev.:	Previous page: 5
File name: 34.100-10.03.04_external_use	Eng. (proj/page): CE / CE	Last print: 15-10-2018	Next page: 7
Page ref.:	Appr. (date/init):	Last edit: 28-12-2016	Total no. of pages: 25



Project title: ERGO 100	Case no.:	Project rev.:	Page 7
Customer:			Scale: 1:1
Page title: Diagram	Dwg. no.: 01	Page rev.: 01	Previous page: 6
File name: 34.100-10.03.04_external_use	Eng. (proj/page): CE / CE	Last print: 15-10-2018	Next page: 8
Page ref.:	Appr. (date/init):	Last edit: 30-12-2016	Total no. of pages: 25

-K1
/6.1
/7.1

Front panel print



Project title: ERGO 100	Case no.:	Project rev.:	Page 8
Customer:			Scale: 1:1
Page title: Diagram	Dwg. no.: 01	Page rev.:	Previous page: 7
File name: 34.100-10.03.04_external_use	Eng. (proj/page): CE / CE	Last print: 15-10-2018	Next page: 9
Page ref.:	Appr. (date/init):	Last edit: 28-12-2016	Total no. of pages: 25

Lists

Component	Article	Type	Description	Position
				/5.6
-B1	AE140-512M	Guard detection		/6.6
-B2	AE140-512M	Guard detection		/6.7
-B3	AE140-86.1M	Magnet induktiv sensor		/8.3
-B4	AE140-86.1M	Magnet induktiv sensor		/8.4
-B5	AE140-86.1M	Magnet induktiv sensor		/8.5
-B6	R20E-501.7	Magnet induktiv sensor		/8.6
-F1	AE140-420.4	Safety relay		/5.6
-K1	AE140-561	Print for VL4 panel		/6.1
-K2	AE140-420.2	Safety Relay delayed stop function		/7.6
-K3	AE140-420	Safety relay		/6.5
-M1	CE101-85	Main motor incl. PTO		/5.2
-M2	CE101-86Z	Lift motor		/5.6
-MB1	CE61-175M	Safety break resistance		/5.3
-Q1	CE101-601	Inverter 4kW		/5.2
-Q2	CE61-420.4	Phase sequence relay		/5.4
-Q3	AE140-420.3	Solid state relay		/5.6
-R1	AE140-601.1	RFI Filter		/5.2
-R2	AE140-601.8	Permanent magnet		/6.1
-S1	CE61-174	Emergency in front panel		/6.2
-S2	CE61-173.1M	Micro switch CE		/6.3
-T1	CE61-414	24VDC Power supply 400VSC/24VDC		/5.7
-W1	CE61-194.1M	POWER		/5.1
-W4	AE140-542.6	24VDC main circuit cable		/5.8

PCSCHEMATIC Automation



From		Cable	To			Type
POWER L2	/5.1	-W1 Black	K1	4	/5.1	POWER
POWER L1	/5.1	-W1 Brown	K1	2	/5.1	POWER
POWER L3	/5.1	-W1 Gray	K1	6	/5.1	POWER
POWER PE	/5.1	-W1 Yellow/green	K1	8	/5.1	POWER
-Q1 L2	/5.2	-W2 Black	-Q3	L2	/5.6	Omformer til elkasse kabel
-Q1 L1	/5.2	-W2 Brown	-Q2	A2	/5.4	Omformer til elkasse kabel
-Q1 L3	/5.2	-W2 Gray	-Q3	L3	/5.6	Omformer til elkasse kabel
-R1 8	/5.2	-W2 Yellow/green			/5.6	Omformer til elkasse kabel
-Q3 T2	/5.6	-W3 Black	-F1	3	/5.6	Conductor
-Q3 T1	/5.5	-W3 Brown	-F1	1	/5.5	Conductor
-Q3 T3	/5.6	-W3 Gray	-F1	5	/5.6	Conductor
-R2 0	/6.6	-W4 Beige	-K3	41	/6.6	Cable to safety relay
-R2 0	/6.7	-W4 Brown	-K3	14	/6.7	Cable to safety relay
-R2 0	/6.7	-W4 Green	-K3	S34	/6.7	Cable to safety relay
-R2 0	/6.6	-W4 Orange	-K3	42	/6.6	Cable to safety relay
-R2 0	/6.5	-W4 Pink	-K3	A1	/6.5	Cable to safety relay
-R2 0	/6.6	-W4 Red	-K3	S33	/6.6	Cable to safety relay
-R2 0	/6.7	-W4 White	-K3	13	/6.7	Cable to safety relay
-R2 0	/6.6	-W4 Yellow	-K3	A2	/6.6	Cable to safety relay
-R2 0	/7.5	-W4 Black	-F1	96	/7.5	Cable termoe relay
-R2 0	/7.5	-W4 Gray	-F1	95	/7.5	Cable termoe relay
-R2 0	/6.2	-W4 Black/blue	-S1	2	/6.1	Conductor, emergency stop to the front panel
-R2 0	/6.2	-W4 Black/gray	-S1	1	/6.2	Conductor, emergency stop to the front panel
-R2 0	/6.1	-W4 Black/red	-S1	1	/6.1	Conductor, emergency stop to the front panel
-R2 0	/6.2	-W4 White/red	-S1	2	/6.2	Conductor, emergency stop to the front panel

PCSCHEMATIC Automation



From			Cable		To			Type
-R2	0	/7.1	-W4	Black/green	-X12	0	/7.1	
-R2	0	/7.1	-W4	Black/white	-X13	0	/7.1	
-R2	0	/7.1	-W4	Black/yellow	-X11	0	/7.1	
-K2	A2	/5.7	-W4	Blue	-R2	0	/6.1	24VDC main circuit cable
-K2	A1	/5.7	-W4	Violet	-R2	0	/6.1	24VDC main circuit cable
-R2	0	/8.4	-W4	Blue/brown	-X22	0	/8.4	Cable PNP JOG
-R2	0	/8.4	-W4	Blue/gray	-X23	0	/8.4	Cable PNP JOG
-R2	0	/8.4	-W4	Blue/orange	-X21	0	/8.4	Cable PNP JOG
-R2	0	/8.3	-W4	Blue/red	-X20	0	/8.3	Cable PNP top
-R2	0	/8.3	-W4	Blue/yellow	-X19	0	/8.3	Cable PNP top
-R2	0	/8.3	-W4	Brown/green	-X18	0	/8.3	Cable PNP top
-R2	0	/7.6	-W4	Gray/brown	-K2	S11	/7.6	Start/stop
-R2	0	/7.6	-W4	Gray/yellow	-K2	S12	/7.6	Start/stop
-R2	0	/6.4	-W4	Gray/green	-X3	0	/6.4	Cable micro switch
-R2	0	/6.3	-W4	Red/brown	-X1	0	/6.3	Cable micro switch
-R2	0	/6.4	-W4	Red/gray	-X2	0	/6.4	Cable micro switch
-R2	0	/6.4	-W4	Red/orange	-X4	0	/6.4	Cable micro switch
-R2	0	/7.4	-W4	Gray/violet	-X15	0	/7.4	Cable to PTO
-R2	0	/7.4	-W4	White/orange	-X14	0	/7.4	Cable to PTO
-R2	0	/8.6	-W4	Green/blue	-X27	0	/8.6	Cable PNP Bowl
-R2	0	/8.6	-W4	White/violet	-X29	0	/8.6	Cable PNP Bowl
-R2	0	/8.6	-W4	White/yellow	-X28	0	/8.6	Cable PNP Bowl
-R2	0	/8.5	-W4	Green/orange	-X25	0	/8.5	Cable PNP bund
-R2	0	/8.5	-W4	Green/red	-X26	0	/8.5	Cable PNP bund
-R2	0	/8.5	-W4	White/blue	-X24	0	/8.5	Cable PNP bund
-R2	0	/7.3	-W4	Orange/gray	-Q1	4	/7.3	Shielded cable
-R2	0	/7.3	-W4	White/gray	-Q1	5	/7.3	Shielded cable
-R2	0	/7.3	-W4	White/green	-Q1	1	/7.3	Shielded cable

PCSCHEMATIC Automation



From			Cable		To			Type
			-W4					Shielded cable
-Q1	U	/5.2	-W5	Brown	-M1	U	/5.2	Cable main motor
-Q1	W	/5.2	-W5	Gray	-M1	W	/5.2	Cable main motor
-Q1	PE	/5.2	-W5	Yellow/green	-M1	PE	/5.2	Cable main motor
-Q1	V	/5.2	-W5	black	-M1	V	/5.2	Cable main motor
-F1	4	/5.6	-W6	Black	-M2	V	/5.6	Cable for lift motor
-F1	2	/5.5	-W6	Brown	-M2	U	/5.5	Cable for lift motor
-F1	6	/5.6	-W6	Gray	-M2	W	/5.6	Cable for lift motor
		/5.6	-W6	Yellow/green	-M2	PE	/5.6	Cable for lift motor
-Q1	BR2	/5.3	-W7	White	-MB1	A2	/5.3	Safety break resistance wire
-Q1	BR1	/5.3	-W7	White	-MB1	A1	/5.3	Safety break resistance wire
-X1	0	/6.3	-W8	Black	-S2	22	/6.3	Cable micro switch
-X3	0	/6.4	-W8	Brown	-S2	14	/6.4	Cable micro switch
-X4	0	/6.4	-W8	White	-S2	13	/6.4	Cable micro switch
-X2	0	/6.4	-W8	blue	-S2	21	/6.3	Cable micro switch
-K3	S22	/6.6	-W9	Orange/brown	-X6	0	/6.6	Conductor
-K3	S11	/6.6	-W9	Yellow/brown	-X5	0	/6.6	Conductor
-K3	S12	/6.7	-W10	White/brown	-X9	0	/6.7	Conductor
-K3	S21	/6.7	-W10	White/green	-X10	0	/6.7	Conductor
-X8	0	/6.6	-W11	Black	-B1	3	/6.6	Cable bowl detection
-X5	0	/6.6	-W11	Blue	-B1	1	/6.6	Cable bowl detection

PCSCHEMATIC Automation



From			Cable		To			Type
-X6	0	/6.6	-W11	Brown	-B1	2	/6.6	Cable bowl detection
-X7	0	/6.6	-W11	Gray	-B1	4	/6.6	Cable bowl detection
-X8	0	/6.6	-W12	Black	-B2	2	/6.7	Cable bowldetection
-X10	0	/6.7	-W12	Blue	-B2	4	/6.7	Cable bowldetection
-X9	0	/6.7	-W12	Brown	-B2	3	/6.7	Cable bowldetection
-X7	0	/6.6	-W12	Gray	-B2	1	/6.7	Cable bowldetection
-X12	0	/7.1	-W13	Black/green	-Q2	14	/7.1	Conductor
-X13	0	/7.1	-W13	Black/white	-Q3	B2	/7.1	Conductor
-X11	0	/7.1	-W13	Black/yellow	-Q2	12	/7.1	Conductor
-Q2	11	/7.1	-W14	Black/ green	-Q3	A2	/7.1	Conductor
-Q2	21	/7.1	-W14	Black/ yellow	-Q3	A1	/7.1	Conductor
-X15	0	/7.4	-W15	Blue	-M1	2	/7.4	PTO kabel
-X14	0	/7.4	-W15	Brown	-M1	1	/7.4	PTO kabel
-X19	0	/8.3	-W16	Black	-B3		/8.3	PNP Sensor cable top
-X20	0	/8.3	-W16	Blue	-B3		/8.3	PNP Sensor cable top
-X18	0	/8.3	-W16	Brown	-B3		/8.3	PNP Sensor cable top
-X22	0	/8.4	-W17	Black	-B4		/8.4	PNP Sensor cable JOG
-X23	0	/8.4	-W17	Blue	-B4		/8.4	PNP Sensor cable JOG
-X21	0	/8.4	-W17	Brown	-B4		/8.4	PNP Sensor cable JOG
-X25	0	/8.5	-W18	Black	-B5		/8.5	PNP Sensor cable bottom
-X26	0	/8.5	-W18	Blue	-B5		/8.5	PNP Sensor cable bottom

PCSCHEMATIC Automation



From		Cable		To		Type		
-X24	0	/8.5	-W18	Brown	-B5	/8.5	PNP Sensor cable bottom	
-X28	0	/8.6	-W19	Black	-B6	/8.6	PNP Sensor cable bowl	
-X29	0	/8.6	-W19	Blue	-B6	/8.6	PNP Sensor cable bowl	
-X27	0	/8.6	-W19	Brown	-B6	/8.6	PNP Sensor cable bowl	
-K2	57	/7.6	-W20	Gra/brown	-X16	0	/7.6	Conductor
-K2	58	/7.6	-W20	Yellow/gray	-X17	0	/7.6	Conductor
-X16	0	/7.6	-W21	Gray/brown	-Q1	SD1	/7.6	Conductor
-X17	0	/7.6	-W21	Gray/yellow	-Q1	SD2	/7.6	Conductor



Page no.	Title	Page remarks	Revision	Last edit
1	front page			28-12-2016
2	Indeks			28-12-2016
3	Table of contents			15-10-2018
4	Diagram			15-10-2018
	Diagram			
5	Diagram		01	15-10-2018
6	Diagram			28-12-2016
7	Diagram		01	30-12-2016
8	Diagram			28-12-2016
	Lists			
9	Parts List			30-12-2016
10	Component list			30-12-2016
11	Cable list			30-12-2016
16	Comments (log)			15-10-2018

PCSCHEMATIC Automation




Page no.	Title	Page remarks	Revision	Last edit
	Arrangement			
18	Component placement			28-12-2016
19	Cable connection			05-01-2017
	PCB diagram			
20	Diagram			28-12-2016
21	Diagram			28-12-2016

PCSCHEMATIC Automation



Arrangement



400VAC/24VDC
power supply
Part no. CE61-414


Safety relay
delayed
stop function
Part no. AE140-420.2

Safety relay
Part no. AE140-420


Safety relay
part no. AE140-420.4

Phase sequence relay
part no. CE61-420.4

Solid state relay
part no. CE140-420.3



Project title: ERGO 100	Case no.:	Project rev.:	Page 18
Customer:			Scale: 1:1
Page title: Component placement	Dwg. no.: 08	Page rev.:	Previous page: 17
File name: 34.100-10.03.04_external_use	Eng. (proj/page): CE / CE	Last print: 15-10-2018	Next page: 19
Page ref.:	Appr. (date/init):	Last edit: 28-12-2016	Total no. of pages: 25



Notes:

1: The relay must be set to 2 seconds.
 i.e. all DIP switches must be set to the left
 and timer 1 & 2 to "F"

2: Reset button on the control unit should be affected for test

